

Model CPT2500



With USB adapter and software

Applications

Calibration service companies and service industry Quality assurance

Recording and monitoring of pressure processes

Recording and monitoring of pressure processes Measurement of pressure peaks



Model CPT2500 USB pressure transmitter with model CPA2500 USB adapter



Special features

Recording interval can be set from 1 ms ... 10 s
Measuring ranges from 0 ... 25 mbar to 0 ... 1,000 bar
Accuracy: 0.2 %, optional 0.1 %
(incl. calibration certificate)
No external voltage supply required
Software for recording of measured values, calibration
and evaluation

Description

Extensive application possibilities

The CPT2500 USB pressure transmitter is suitable for connection to any PC with a USB port, via the CPA2500 USB adapter.

For the USB adapter there are stainless steel pressure transmitters available with measuring ranges up to 1,000 bar. The USB adapter automatically detects the measuring range of the currently connected pressure transmitter and ensures a highly accurate pressure measurement.

Functionality

The measurement interval for pressure recording can be set in the range of 1 ms ... 10 s. With a recording interval of more than 5 ms the following data is recorded in addition to the current measured value:

the mean value over the recording interval

the maximum and minimum value during the recording interval

Thus pressure peaks within the overall recording interval can be very easily identified.

It is also possible to set start and stop conditions for the

recording. In this way it is possible to detect pressure peaks with a resolution of up to 1 ms.

The CPT2500 is a thus very well suited to all applications where, over a limited time span, pressure processes must be recorded and analysed with high resolution.

Software

The USBsoft2500 and USB ScanSoft software are delivered as standard with the USB adapter. With it, all settings for recording the pressure process can be made. The recorded measured values can be graphically displayed and evaluated.

In addition to the USBsoft2500 and USB ScanSoft software, WIKA-CAL calibration software for calibration tasks is also available. Using this software, the data is automatically transferred into a printable calibration certificate. Furthermore, WIKA-CAL also offers, over and above PC-supported calibration, the management of the calibration and instrument data in an SQL database. For data transfer, a USB interface is available.



Model CPT2500

Complete service case

For easy transport and safe storage, the USB adapter is delivered in a compact transport case, which can also hold one or more pressure transmitters.

Certified accuracy

For each reference pressure sensor, the accuracy for the complete measuring chain is certified by a factory calibration certificate which accompanies the instrument. On request, we can provide a DKD/DAkkS calibration certificate for this instrument.

Specifications

USB pressure to	ransm <u>itt</u>	er mode	I CPT28	500 (c <u>o</u> r	nplete n	neasurir	ig cha <u>in</u>)	
Measuring range	mbar	0 25	0 0	0 60	0 100	0 160	0 250	0 400	0 600
Overpressure limit	mbar	500	500	500	1000	1500	2000	2000	4000
Burst pressure	mbar	1000	1000	1000	2000	2000	2400	2400	4800
Resolution	dependant on pressure range (max. 4 1/2-digit)								
Measuring range	bar	0 1	0 1,6	0 2,5	0 4	0 6	0 10	0 16	0 25
Overpressure limit	bar	5	10	10	17	35	35	80	50
Burst pressure	bar	6	12	12	20,5	42	42	96	96
Resolution	dependant on pressure range (max. 4 1/2-digit)								
Measuring range	bar	0 40	0 60	0 100	0 160	0 250	0 400	0 600	0 1.000
Overpressure limit	bar	80	120	200	320	500	800	1.200	1.500
Burst pressure	bar	400	550	800	1000	1200	1700	2400	3000
Resolution	dependant on pressure range (max. 4 1/2-digit)								
Type of pressure	Relative pressure, {absolute pressure from 0 25 bar abs. and vacuum from -1 +24 bar}								
Accuracy of the measuring chain	0.2 % FS (resolution 4-digit); {optional: 0.1 % FS (resolution 4 1/2-digit)}								

 $^{\{\,\}}$ Items in curved brackets are optional extras for an additional price.

	sure sensor model CPT2500		
Process connection 1)	G ½ B; {flush diaphragm (G 1 for 0.1 up to 1.6 bar) or various connection adapters on request}		
Pressure units	mbar, bar, Pa, kPa, MPa, mmHg, psi, inHg (0 °C), inHg (60 °F), mWs; (depending on the measuring range, selectable)		
Material			
Wetted parts	Stainless steel or Elgiloy [®] , (> 25 bar with additional NBR seal) ²⁾ Flush diaphragm version: stainless steel {Hastelloy C4}; O-ring: NBR {FKM/FPM or EPDM}		
Internal transmission fluid	Synthetic oil (only for measuring ranges up to 16 bar or flush diaphragm) {Halocarbon oil for oxygen applications}; {Listed by FDA for food industry}		
Sensor specification			
Accuracy per year	≤ 0.2 % of span at reference conditions ³⁾		
Compensated range	0 80 °C		
Mean temperature coefficient	≤ 0.2 % of span/10 K (outside of reference conditions)		
Measuring rate	1,000 measurements/s		



Model CPT2500

Permissible ambient con-	ditions
Medium temperature	-25 +100 °C ⁴⁾
Operating temperature	-20 +80 °C
Storage temperature	-40 +100 °C ⁴⁾
Relative humidity	0 95 % r. h. (non-condensing)
Case	
Material	Stainless steel
Dimensions	see technical drawings
Weight	approx. 220 g

- {} Items in curved brackets are optional extras for an additional price.
- 1) As an oxygen version, a flush diaphragm model is not available. In an oxygen version, the model CPT2500 is only available in gauge pressure ranges ≥ 0.25 bar, with media temperatures between -10 ... +50 °C and using stainless steel or Elgiloy® wetted parts.
- 2) For pressure measuring ranges 0 ... 25 mbar, 0 ... 40 mbar and 0 ... 60 mbar all wetted parts are made of stainless steel, silicium, aluminium, gold, silicone.
- 3) Reference conditions: 15 ... 25 °C
- 4) For pressure measuring ranges 0 ... 25 mbar, 0 ... 40 mbar and 0 ... 60 mbar the medium temperature and storage temperature are limited to +80 $^{\circ}$ C.

USB adapter model CPA2500	
Communication	
PC connection	Standard USB connector (type A)
Electrical sensor	Circular connector, 7-pin, M16 x 0.75
connection	
Recording interval	1 ms 10 s, adjustable via software
Recording options	selectable start/stop conditions, pre-trigger, stop-delay
Voltage supply	
Power supply	Supply via USB port
Permissible ambient conditions	
Operating temperature	-25 +50 °C
Storage temperature	-25 +70 °C
Relative humidity	0 95 % r. h. (non-condensing)
Case	
Dimensions	see technical drawings
Weight	арргох. 120 g

CE conformity,	approvals, certificates
CE conformity for the mo	odel CPT2500 USB pressure transmitter
Pressure equipment directive	97/23/EC, module A, pressure accessory
EMC directive	2004/108/EC, EN 61326 Emission (group 1, class B) and interference immunity (commercial applications, laboratories, service centres and workshops)
CE conformity for the mo	odel CPA2500 USB adapter
EMC directive	2004/108/EC, EN 61326 Emission (group 1, class B) and interference immunity (controlled electromagnetic environment)
Approvals	
GOST-R	Import certificate, Russia



Model CPT2500

Certificates


Calibration Standard: 3.1 calibration certificate per DIN EN 10204

Option: DKD/DAkkS calibration certificate


Approvals and certificates, see website

Dimensions in mm

USB adapter model CPA2500



USB pressure transmitter model CPT2500





Model CPT2500


USBsoft2500 and USB ScanSoft configuration and evaluation software

The USBsoft2500 software is required for the operation of the model CPT2500 USB pressure transmitter in connection with the model CPA2500 USB adapter. This enables the configuration of the pressure transmitter as well as the selection of the various recording settings.

The software also allows different start/stop conditions to be defined, in order to easily identify, for example, a single pressure peak.

Graphical evaluation of the measured data (including mean, min- and max-values), in addition the measured data can also be exported to other software. Several series of measurements can be displayed in a single chart.

Using software USB ScanSoft, several CPT2500 in combination with model CPA2500 USB adapter can be run parallel. For each CPT2500 one CPA2500 is required.



Performance data

Recording interval of 1 ms ... 10 s

Data export to other programs e.g. Excel®

Languages: German, English, Spanish and Czech

System requirements for USBsoft2500

CPU with at least 1 GHz

At least 20 MB free hard disc space

CD-ROM drive

At least 256 MB RAM

Windows® operating system 95, 98, NT 4.0 (with Service Pack 3.0 or higher), 2000, XP, Vista or 7 USB port

System requirements for USB ScanSoft

CPU with at least 1.2 GHz

At least 100 MB free hard disc space

CD-ROM drive

At least 1 GB RAM

Windows® operating system XP (SP 3), Vista (SP2) or 7 (SP1)

USB port

Windows® is a registered trademark of Microsoft Corporation in the United States and other countries





Model CPT2500

WIKA-CAL calibration software

Easy and fast creation of a high-quality calibration certificate

The WIKA-CAL calibration software is used for generating calibration certificates or logger protocols for pressure measuring instruments and is available as a demo version for a cost-free download.

A template helps the user and guides him through the creation process of a document.

In order to switch from the demo version to a full version of the respective template, a USB key with the template has to be purchased.

The pre-installed demo version automatically changes to the selected full version when the USB key is inserted and is available as long as the USB key is connected to the computer.

Creation of calibration certificates for mechanical and electronic pressure measuring instruments

A calibration assistant guides you through the calibration Automatic generation of the calibration steps

Generation of 3.1 certificates in accordance with

DIN EN 10204

Creation of logger protocols

User-friendly interface

Languages: German, English, Italian and more due with software updates

For further information see data sheet CT 95.10



Calibration certificates can be created with the Cal-Template and logger protocols can be created with the Log-Template.



Cal Demo

Generation of calibration certificates limited to 2 measuring points, with automatic initiation of pressures via a pressure controller.



Cal Light

Generation of calibration certificates with no limitations on measuring points, without automatic initiation of pressures via a pressure controller.



Log Demo

Creation of data logger test reports, limited to 5 measured values.



Log

Creation of data logger test reports without limiting the measured values.



	Certificate No. 000000 Jacquin No.
Measurement results Measurement	
1000	
Statement of compliance	
Copyriant of the specificational in the trapport of the transport of the specification and	

robbies beans			V	VIKAL
			LNINC	0000000
			LIGHT.	00000005
Device under test				
Profiling Entertail phose				
		14		
Name of Street				
Name No.		WAR		
Name of the least		a. mary		
The State of the S		107.0		
SOMMON .				
Measurement cone Measteringurgen	Home			
Exception and the second				
Posts Date	Parist Street			
Parties.	1079			
Paul .	Males			
Name of State of Stat				
22.00				
Measurement resu Measurement resu	is .			
Frency	Name of the last			
DANNER	Development Mark			
100 DO F OF 15	120			
ATTENDED TO STATE	100			
STREET, STREET	1500			
NO. SECTO	0.0000			796 111
Witness of the last of the las	A REPORT OF THE PARTY OF			



Model CPT2500

Scope of delivery

- USB pressure transmitter model CPT2500
- USB adapter model CPA2500
- Software USBsoft2500 and USB ScanSoft
- Transport case
- Operating instructions
- 3.1 calibration certificate per DIN EN 10204

Options

- DKD/DAkkS certified accuracy
- Sensors for oxygen applications

Accessories

Connection adapters

- Various pressure adapters
- MINIMESS® quick-connect process connection system

Pressure generation

- Pneumatic test pumps
- Hydraulic test pumps

Software

■ WIKA-CAL calibration software



Transport case with USB pressure transmitter and USB adapter

Ordering information

Model / Unit / Measuring range / Accuracy / Process connection / Extension cable / Type of certificate / Accessories / Additional order information